

KERN OBS 105

KERN

The school microscope – for the first steps in microscopy and for use in biology lessons



Category

Brand	Optics
Product category	Microscope
Product group	Compound microscope
Product family	OBS-1

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	130×300×310 mm
Optical system	Finite
Tube type	Monocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Lens quality	achromatic
Standard objectives	4× 10× 40×
Nosepiece screw-in locations	4
Eyepieces fixed	✓
Contrasting methods	Bright field
Interpupillary distance [Max]	75 mm
Interpupillary distance [Min]	55 mm

Ocular

Ocular field width	WF
Eye point	Standard
Ocular magnifications	10 x
Ocular visual field	18 mm
Ocular diameter	23,2 mm

Focussing

Fine drive minimum	0,00025 mm
Field of view [Min]	0,45 mm
Field of view [Max]	4,5 mm
Focusing mechanism	coaxial coarse and fine drive

Illumination

Illumination intensity transmitted light	0,5 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Illumination dimmable	Transmitted light
Aperture diaphragm	✓
Filter possible	✓

Power Supply

Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	6 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO UK
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	4 h
Battery	3×1.2V AA
Battery / accumulator type	NiMH
Battery connection	Plug-in terminals

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	410×280×210 mm
Net weight	3,138 kg
Shipping method	Parcel service
Net weight approx.	3,2 kg
Gross weight approx.	4,0 kg
Shipping weight	4,8 kg

KERN OBS 105



The school microscope – for the first steps in microscopy and for use in biology lessons

Objective

Objectives - Details	Objective Achromatic 10 x / 0,25 anti-fungus Objective Achromatic 4 x / 0,1 anti-fungus Objective Achromatic 40 x / 0,65 spring, anti-fungus
----------------------	--

Pictograms

STANDARD

