## KERN OBS 112



The school microscope – for the first steps in microscopy and for use in biology lessons



Category	
Brand	Optics
Product categoriy	Microscope
Product group	Compound microscope
Product family	OBS-1

Approval	
CE mark	✓

Construction	
Dimension (W×D×H)	130×300×310 mm
Optical system	Finite
Tube type	Monocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Lens quality	achromatic
Standard objectives	4× 10× 40×
Nosepiece screw-in locations	3
Eyepieces fixed	✓
Contrasting methods	Bright field

Ocular	
Ocular field width	WF
Eye point	Standard
Ocular magnifications	10 x
Ocular visual field	18 mm
Ocular diameter	23,2 mm

Focussing	
Fine drive minimum	0,0025 mm

Field of view [Min]	0,45 mm
Field of view [Max]	4,5 mm
Focusing mechanism	coaxial coarse and fine drive

Illumination	
Illumination intensity transmitted light	0,5 W
Illumination type transmitted light	LED
Illuminance	Transmitted light
Aperture diaphragm	✓
Filter possible	✓

Power Supply	
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	3V, 500mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO UK

-5 °C
40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	390×250×190 mm
Net weight	2,138 kg
Shipping method	Parcel service
Net weight approx.	2,2 kg
Gross weight approx.	3,0 kg
Shipping weight	3,7 kg

Objective	
Objectives - Details	Objective Achromatic 10 x / 0,25 anti-fungus Objective Achromatic 4 x / 0,1 anti-fungus Objective Achromatic 40 x / 0,65 spring, anti-fungus

1

## KERN OBS 112



The school microscope - for the first steps in microscopy and for use in biology lessons

## Pictograms

## **STANDARD**









