

KERN OZP 551



Individuality, variety and flexible working through our modular construction system ▶ Stereo microscope heads



Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	310×300×220 mm
Net weight	2,4514 kg
Shipping method	Parcel service
Net weight approx.	2,6 kg
Gross weight approx.	3,0 kg
Shipping weight	4,1 kg

Pictograms

STANDARD



Category

Brand	Optics
Product category	Microscope
Product group	Stereo Microscope-Head
Product family	OZB-M

Construction

Optical system	Greenough
Tube type	Binocular
Tube angle of inclination	35°
Tube 360° rotation	✓
Diopter adjustment	both-sided
Interpupillary distance [Max]	76 mm
Interpupillary distance [Min]	52 mm

Ocular

Ocular field width	HSWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	23 mm
Ocular diameter	30 mm

Focussing

Working distance	108 mm
Zoom [Min]	0,6 x
Zoom [Max]	5,5 x
Magnification ratio	9,2:1
Field of view [Min]	38,3 mm
Field of view [Max]	4,2 mm
Sample height [Max]	110 mm
Standard total magnification [Min]	6 x
Standard total magnification [Max]	55 x