

KERN OZP 556

KERN

Professional and powerful – thanks to its extremely large magnification range, strong illumination and first-class optics



Category

Brand	Optics
Product category	Microscope
Product group	Stereo microscope
Product family	OZP-5

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	330×285×470 mm
Optical system	Greenough
Tube type	Binocular
Tube angle of inclination	35°
Tube 360° rotation	✓
Diopter adjustment	both-sided
Diopter adjustment [Min]	-6
Diopter adjustment [Max]	6
Contrasting methods	Bright field Darkfield (optional)
Interpupillary distance [Max]	76 mm
Interpupillary distance [Min]	52 mm

Ocular

Ocular field width	HSWF
Ocular magnifications	10 x
Ocular visual field	23 mm
Ocular diameter	30 mm

Focussing

Torque regulation	✓
Working distance	108 mm

Zoom [Min]	0,6 x
Zoom [Max]	5,5 x
Magnification ratio	9,2:1
Field of view [Min]	4,2 mm
Field of view [Max]	38,3 mm
Focusing mechanism	coarse drive
Sample height [Max]	110 mm
Standard total magnification [Min]	6 x
Standard total magnification [Max]	55 x

Illumination

Illumination type incident light	LED
Illumination intensity incident light	3 W
Illumination intensity transmitted light	3 W
Illumination type transmitted light	LED
Illuminance	Reflected light Transmitted light

Power Supply

Input voltage power supply / power [Max]	110 - 220 V
Input voltage device / power [Max]	110 - 220 V
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
	AUS
Plug-in power supply / adapter for countries - optional	UK US CH

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	385×370×330 mm
Net weight	4,6816 kg
Shipping method	Parcel service
Net weight approx.	4,8 kg
Gross weight approx.	6 kg
Shipping weight	9,4 kg


KERN OZP 556



Professional and powerful – thanks to its extremely large magnification range, strong illumination and first-class optics

Pictograms

STANDARD



OPTION

