KERN ORA 2AB



Refractive index measurement for laboratories and the industry



Category	
Brand	Optics
Product categoriy	Refractometer
Product group	Analogue refractometer
Product family	ORA-AL

Measuring System	
Measuring method	Light refraction
Area of application	Alcohol
Appropriate calibration liquid	0 % (distilled water)
Measurement temperature [Min] (°C)	20 °C
Measurement temperature [Max] (°C)	20 °C
Scale percent by mass	✓
Readout percent by mass	1 % (w/w)
Measuring range percent by mass [Min]	0 % (w/w)
Measuring range percent by mass [Max]	50 % (w/w)
Readout percent by mass II	2,5 % (w/w)
Measuring range percent by mass II [Min]	50 % (w/w)
Measuring range percent by mass II [Max]	80 % (w/w)

Construction	
Dimension (W×D×H)	198×40×40 mm
Refractometer type	Handheld refractometer
Scale - Display type	Analogue

Functions	
IP protection - complete device	<u>-</u>

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C
Packing & Shipping	
Dimensions transport container (W×D×H)	205×75×55 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	215×94×65 mm
Net weight	0,26772 kg
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	0,35 kg
Shipping weight	0,32 kg

Environmental conditions

Services (optional)	
Article number for factory calibration	961-290

Pictograms

STANDARD



1