

KERN ORM 2UN

KERN

Digital measurement of refraction index for universal application



Category

Brand	Optics
Product category	Refractometer
Product group	Digital refractometer
Product family	ORM-UN

Measuring System

Automatic temperature compensation (ATC)	✓
Measuring method	Total reflection
Area of application	Urine
Appropriate calibration liquid	0 % (distilled water)
Measurement temperature [Min] (°C)	0 °C
Measurement temperature [Max] (°C)	40 °C
Brix scale	✓
Readout Brix	0,1 %
Measuring range Brix [Min]	0 %
Measuring range Brix [Max]	50 %
Accuracy Brix	±0,2 %
Scale for Refractive index	✓
Readout refractive index	0,0001 nD
Measuring range refractive index [Min]	1,3330 nD
Measuring range refractive index [Max]	1,4200 nD
Accuracy refractive index	±0,0003 nD
Scale urine (s. g. dog)	✓
Readout urine (s. g. dog)	0,001
Measuring range urine (s. g. dog) [Min]	1,000
Measuring range urine (s. g. dog) [Max]	1,060
Accuracy urine (s. g. dog)	±0,002

Scale urine (s. g. cat)	✓
Readout urine (s. g. cat)	0,001
Measuring range urine (s. g. cat) [Min]	1,000
Measuring range urine (s. g. cat) [Max]	1,060
Accuracy urine (s. g. cat)	±0,002

Approval

CE mark	✓
---------	---

Construction

Dimension (W×D×H)	121×58×25 mm
Refractometer type	Handheld refractometer
Scale - Display type	Digital

Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	60 sec
IP protection - complete device	IP65
Automatic temperature compensation	✓

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	1.300 mAh
Battery voltage	1,5 V

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Dimensions transport container (W×D×H)	170×110×50 mm
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	170×110×50 mm
Net weight	0,14 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,35 kg
Shipping weight	0,31 kg

KERN ORM 2UN



Digital measurement of refraction index for universal application

Services (optional)

Article number for factory calibration	961-290
--	---------

Pictograms

STANDARD

