## KERN PCD 300-3



# High-resolution precision balance with removable display for maximum flexibility



Category	
Brand	KERN
Product categoriy	Laboratory balance
Product group	Precision balance
Product family	PCD
Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	350 g
Readability [d]	0,001 g
Resolution	350.000
Linearity	± 0,005 g
Reproducibility	0,002 g
Tare range	350 g
Default unit	g
Units	g gn dwt tl (Tw) tl (HK) ozt ct mo oz ffa tol
Adjustment options	Adjusting with external weight
Recommended adjusting weight	350 g (F1)
Stabilization time	4 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,005 g
Maximum creep (15 minutes)	10 mg

Maximum creep (30 minutes)	20 mg
Approval	
CE mark	1
Display	
Display type	LCD
Display backlight	1
Display digit height	21 mm
Languages of the user interface	English
Construction	
Dimensions device (W×D×H)	165×280×75 mm
Dimension display device (W×D×H)	140×46×75 mm
Dimension housing (W×D×H)	165×280×75 mm
Dimensions rectangular draught shield - inner (W×D×H)	146×146×80 mm
Dimensions rectangular draught shield - outer (W×D×H)	157×157×80 mm
Dimensions completely mounted (W×D×H)	165×280×141 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	plastic
Material draught shield	plastic
Dimensions weighing surface (Ø)	105 mm
Display device cable length	1,2 m
Levelling feet adjustable	1
Stand height	250 mm
Stand inclinable	1
Functions	
Number of keys for operation	5
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery	3 min off
mode/rechargeable battery mode	
Percentage determination	manual (multi) ✓
Counting function	v ./
Function for averaging under	v
unstable weighing conditions	$\checkmark$
Peak function	1
Recipe/summing level	Rez A (Net total)
Underfloor weighing	None
Interfaces	RS-232 standard

## KERN PCD 300-3



High-resolution precision balance with removable display for maximum flexibility

#### Counting

Smallest piece weight when piece counting - laboratory conditions	2 mg
Smallest piece weight when piece counting - normal conditions	20 mg
Reference quantity	5, 10, 20, 25, 50
Counting resolution (laboratory conditions)	175.000

### Power Supply

11.2	
Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	9 V, 300 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	US
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	12 h
Rechargeable battery operating time - backlight off	24 h
Battery	9 V block
Battery connection	Plug-in terminals
Battery operating time	12 h

#### Environmental conditions

80 %
5 °C
35 °C
-20 °C
60 °C

### Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	240×530×160 mm
Net weight	1 kg
Shipping method	Parcel service
Net weight approx.	1,00 kg
Gross weight approx.	2,4 kg
Shipping weight	4,1 kg

Services (optional)	
Article number for DAkkS calibration	963-127
Article number for certificate of conformity (verification)	969-517

#### Pictograms

#### STANDARD



#### OPTION

<b>kkS</b>
DAYS