

# KERN SFE 100K-2XLNM

# KERN

Platform scale with IP65 dust and spray protection, verification optional



## Category

|                  |                  |
|------------------|------------------|
| Brand            | KERN             |
| Product category | Industrial scale |
| Product group    | Platform scale   |
| Product family   | SFE              |

## Measuring System

|  |                                |
|--|--------------------------------|
| Construction type of the scale           | Single-range balance           |
| Weighing system                          | Strain gauge                   |
| Weighing capacity [Max]                  | 150 kg                         |
| Readability [d]                          | 0,05 kg                        |
| Resolution                               | 3.000                          |
| Linearity                                | ± 0,05 kg                      |
| Reproducibility                          | 0,05 kg                        |
| Tare range                               | 149,95 kg                      |
| Default unit                             | kg                             |
| Units                                    | kg                             |
| Units (if device is conformity assessed) | kg                             |
| Minimum weight [Min]                     | 1 kg                           |
| Adjustment options                       | Adjusting with external weight |
| Recommended adjusting weight             | 150 kg (M1)                    |
| Stabilization time                       | 2 s                            |
| Warm-up time                             | 10 min                         |
| Eccentric loading at 1/3 [Max]           | 0,05 kg                        |
| Loadcell type                            | aluminium IP65 silicone-coated |

## Approval

|  |     |
|--|-----|
| CE mark                                    | ✓   |
| Pattern approval for conformity assessment | ✓   |
| Accuracy classe                            | III |

|   |         |
|---|---------|
| Verification scale interval [e]         | 0,05 kg |
| Conformity assessment possible ex works | ✓       |

## Display

|                      |       |
|----------------------|-------|
| Display type         | LCD   |
| Display backlight    | ✓     |
| Display digit height | 22 mm |

## Construction

|                                      |                  |
|--------------------------------------|------------------|
| Dimension display device (W×D×H)     | 195×118×83 mm    |
| Dimensions weighing platform (W×D×H) | 650×500×136 mm   |
| Material display housing             | stainless steel  |
| Material weighing plate              | stainless steel  |
| Material platform                    | steel, varnished |
| Dimensions weighing surface (W×D)    | 650×500 mm       |
| Cable length                         | 2,5 m            |
| Display device cable length          | 3 m              |
| Material load cell(s)                | aluminium        |
| Levelling feet adjustable            | ✓                |
| Wall mount                           | ✓                |

## Functions

|   |                         |
|---|-------------------------|
| Number of keys for operation                              | 6                       |
| Tare function   | manual (single & multi) |
| Tolerance weighing  | ✓                       |
| Tolerance weighing - type of signal                       | acoustically<br>visual  |
| Function for averaging under unstable weighing conditions | ✓                       |
| Recipe/summing level                                      | Rez A (Net total)       |
| Sum memory function                                       | ✓                       |
| IP protection - complete device                           | -                       |
| IP protection - display                                   | IP65                    |
| IP protection - load cell                                 | IP65                    |
| IP protection - platform                                  | no IP protection        |

## Power Supply

|   |                         |
|---|-------------------------|
| Input voltage power supply / power [Max]                                  | 220 V - 240 V AC, 50 Hz |
| Input voltage device / power [Max]  | 12 V, 500 mA            |
| Plug-in power supply type   | Power adapter           |
| Supplied power supply   | Battery & Power supply  |
| Plug-in power supply / adapter for countries - included with the delivery | EURO<br>UK<br>US        |

# KERN SFE 100K-2XLNM



Platform scale with IP65 dust and spray protection, verification optional

|   |                   |
|---|-------------------|
| Plug-in power supply / adapter for countries - optional | EURO              |
|   | AUS               |
|   | UK                |
|   | US                |
|   | CH                |
| Rechargeable battery charging time                      | 12 h              |
| Rechargeable battery operating time - backlight on      | 10 h              |
| Rechargeable battery operating time - backlight off     | 35 h              |
| Battery / accumulator type                              | NiMH              |
| Battery connection                                      | Plug-in terminals |

## Environmental conditions

|                               |        |
|-------------------------------|--------|
| Humidity of environment [Min] | 0 %    |
| Humidity of environment [Max] | 80 %   |
| Ambient temperature [Min]     | -10 °C |
| Ambient temperature [Max]     | 40 °C  |
| Storage temperature [Min]     | -20 °C |
| Storage temperature [Max]     | 60 °C  |

## Packing & Shipping

|                              |                 |
|------------------------------|-----------------|
| Readability force [d] (N)    | 1 d             |
| Dimensions packaging (W×D×H) | 670×1040×250 mm |
| Net weight                   | 20,2 kg         |
| Shipping method              | Parcel service  |
| Net weight approx.           | 22 kg           |
| Gross weight approx.         | 26 kg           |
| Shipping weight              | 34,8 kg         |

## Services (optional)

|   |         |
|---|---------|
| Article number for adjustment at the location of installation | 961-249 |
| Article number for conformity assessment                      | 965-229 |
| Article number for DAkkS calibration                          | 963-129 |
| Article number for certificate of conformity (verification)   | 969-517 |

## Pictograms

### STANDARD



### OPTION



### FACTORY

