

KERN TVL 100FHS71

KERN

The practical all-in-one package for rapid, simple testing



Type of drive	manual crank handle
Tensile/compressive force [Max]	100 N
Traverse distance [Max]	200 mm
Maximum clamp width	10 mm

Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min
Hold function	✓
Peak function	✓
Statistic function	✓
Limit-setting function	✓
Memory function	✓
Interfaces	RS-232 standard

Power Supply

Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	12 V, 400 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Rechargeable battery charging time	4 h
Rechargeable battery operating time - backlight on	10 h
Rechargeable battery operating time - backlight off	12 h
Battery / accumulator type	NiMH

Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	400×260×280 mm
Net weight	6,5 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	7 kg
Shipping weight	7 kg

Services (optional)

Article number for DAkkS calibration (tensile force)	963-161
--	---------

Category

Brand	Sauter
Product category	Force measurement
Product group	Force-Measuring Bundle

Measuring System

Default unit	N
Tolerance (% of [Max])	0,5%
Measuring range force [Max] (N)	100 N
Readability force [d] (N)	0,05 N
Directions of force	tension compression
Measuring head measuring frequency	2 kHz
Length measuring device	Length measuring device with display
Overload protection (% of [Max])	150%
Internal data memory: Number of value groups	1
Internal data memory: Number of individual values	10

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display digit height	10 mm
Screen reversible	✓

Construction

Generated force [Max]	100 N
-----------------------	-------

KERN TVL 100FHS71



The practical all-in-one package for rapid, simple testing

Article number for DAkkS calibration (compressive force) 963-261

Article number for DAkkS calibration (tensile force/ compressive force) 963-361

Article number for factory calibration (tensile force) 961-161

Article number for factory calibration (compressive force) 961-261

Article number for factory calibration (tensile force/ compressive force) 961-361

Pictograms

STANDARD



OPTION

