## KERN TVL-XLS



Manual test stand for highly accurate tensile and compressive force measurements, with length measurement



Dimensions packaging (W×D×H)	200×300×800 mm
Net weight	11,3 kg
Shipping method	Parcel service
Net weight approx.	12 kg
Gross weight approx.	14 kg
Shipping weight	14 kg

## Pictograms

## STANDARD





Category	
Brand	Sauter
Product categoriy	Test bench
Product group	Manual test stand
Product family	TVL

Measuring System	
Measuring range force [Max] (N)	500 N
Directions of force	tension compression
Length measuring device	Length measuring device with display
Measurable length [Max]	54 cm
Overload protection (% of [Max])	150%

Construction		
Dimension housing (W×D×H)	200×300×800 mm	
Dimensions completely mounted (W×D×H)	200×300×800 mm	
Material	coated metal	
Material housing	metal, lacquered	
Generated force [Max]	500 N	
Mounting - force application	5 × threaded hole M6	
Mounting - force dissipation	5 × threaded hole M6	
Travel distance per knob rotation (stroke per one turn)	3 mm	
Type of drive	manual crank handle	
Tensile/compressive force [Max]	500 N	
Traverse distance [Max]	230 mm	

Packing & Shipping		
Readability force [d] (N)	1 d	