KERN UID 1500K-1DM



High-resolution multi-range pallet scale with a wide range of interfaces, verification optional



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Pallet scale
Product family	UID

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Multi-range balance
Number of weighing ranges	2
Weighing system	Strain gauge
Weighing capacity [Max]	600 kg; 1500 kg
Readability [d]	0,2 kg; 0,5 kg
Resolution	3.000, 3.000
Linearity	± 0,6 kg; 1,5 kg
Reproducibility	0,2 kg; 0,5 kg
Tare range	-1500 kg
Default unit	kg
Units	kg g Ib oz PCS tJ HJ
Units (if device is conformity assessed)	kg
Minimum weight [Min]	4 kg; 10 kg
Adjustment options	Adjusting with external weight
Possible calibration points	1000 kg
Stabilization time	4 s
Warm-up time	10 min; 10 min

Eccentric loading at 1/3 [Max]	1 kg; 2,5 kg
Loadcell type	KELI-SQB-750kg
Load cell connection	4-wire

Approval	
CE mark	✓
Pattern approval for conformity assessment	✓
Accuracy classe	III
Verification scale interval [e]	0,2 kg; 0,5 kg
Conformity assessment possible ex works	✓

Display	
Display type	LCD
Display type	LCD
Display screen size	110×35 mm
Display backlight	✓
Display digit height - smallest digit	25 mm
Display digit height	25 mm
Languages of the user interface	Symbol language

Construction	
Dimension display device (W×D×H)	268×115×80 mm
Dimensions weighing platform (W×D×H)	1190×840×110 mm
Material display housing	Plastics
Material weighing plate	steel, powder-coated
Material platform	steel, powder-coated
Dimensions weighing surface (W×D)	1195×840 mm
Cable length	5 m
Display device cable length	5 m
Allowed cable length display device [Max]	15 m
Material load cell(s)	alloyed steel
Load cells - number	4
Levelling feet adjustable	✓
Wall mount	✓
Stand inclinable	✓

Functions	
Number of keys for operation	4
Auto-off interval(s) in mains power mode	3 min off 5 min 30 min 15 min

1

KERN UID 1500K-1DM



High-resolution multi-range pallet scale with a wide range of interfaces, verification optional

Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 30 min 15 min
Time display	\checkmark
Tare function	manual (single)
Hold function	✓
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Function for averaging under unstable weighing conditions	1
Recipe/summing level	Sum A
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 standard Ethernet (optional, factory) USB (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) USB-Host/Master (optional, factory) Verification plug (optional, factory) Bluetooth BLE (v4.0) (optional, factory)
IP protection - display	IP65
IP protection - load cell	IP67
Counting	

Counting	
Reference quantity	10, 20, 50, 100, 200

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0.4 A max
Input voltage device / power [Max]	12 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	3 h

Rechargeable battery operating time - backlight on	26 h
Rechargeable battery operating time - backlight off	43 h
Battery	no battery
Battery / accumulator type	Pb
Environmental conditions	
Humity of environment [Min]	10 %
Humity of environment [Max]	95 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1240×890×250 mm
Net weight	44 kg
Shipping method	Freight
Net weight approx.	44 kg
Gross weight approx.	65 kg
Shipping weight	65 kg
Services (optional)	
Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130
Article number for certificate of conformity (verification)	969-517

KERN UID 1500K-1DM



High-resolution multi-range pallet scale with a wide range of interfaces, verification optional

Pictograms

STANDARD



OPTION



FACTORY

