# KERN SFB 10K1HIP



## Stainless steel platform scale with IP65/IP67 protection and elevated display



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Stainless steel platform scale
Product family	SFB
Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	10 kg
Readability [d]	0,001 kg
Resolution	10.000
Linearity	± 0,001 kg
Reproducibility	0,001 kg
Tare range	-10 kg
Default unit	kg
Units	kg g Ib Hj, tJ Ib:oz
Units (if device is conformity assessed)	kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	10 kg (M1)
Stabilization time	2 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,001 kg
Maximum creep (15 minutes)	4 g
Maximum creep (30 minutes)	8 g

Loadcell type	stainless steel IP67
Load cell connection	silicone-coated 6-wire
Approval	
CE mark	1
Display	
Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display digit height	52 mm
Construction	
Dimension display device (W×D×H)	266×165×96 mm
Dimensions weighing platform (W×D×H)	300×240×104 mm
Dimensions completely mounted (W×D×H)	300×400×395 mm
Material display housing	stainless steel
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	300×240 mm
Cable length	0 m
Display device cable length	0 m
Allowed cable length display device [Max]	30 m
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	Stainless steels
Levelling feet adjustable	1
Wall mount	✓
Stand height	200 mm
Stand inclinable	1
Functions	
Number of keys for operation	7
	off
Auto-off interval(s) in mains power	5 min
mode	30 min
	15 min 3 min
	3 min
Auto off interval(a) in better	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	30 min
Torrefunction	15 min
Tare function	manual (multi) ✓
Counting function	1

# KERN SFB 10K1HIP



Stainless steel platform scale with IP65/IP67 protection and elevated display

Tolerance weighing	1
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	1
Recipe/summing level	Sum A
Sum memory function	1
Interfaces	RS-232 (optional, factory) Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory)
IP protection - display	IP65
IP protection - load cell	IP67
IP protection - platform	no IP protection

### Counting

Reference quantity	10, 20, 50, 100, 200

Power Supply	
Input voltage power supply / power [Max]	110 V - 230 V AC
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Battery & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	35 h
Battery / accumulator type	Pb
Battery connection	Plug-in terminals


#### Environmental conditions

Humity of environment [Min]	10 %
Humity of environment [Max]	95 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	695×415×225 mm
Net weight	7,5 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	10 kg
Shipping weight	13 kg
Services (optional)	
Article number for adjustment at	961-248
the location of installation	701-240
Article number for DAkkS	963-128
calibration	,00 120
Article number for certificate of	969-517
conformity (verification)	

### Pictograms

#### STANDARD



#### OPTION

## DAkkS

+3 DAYS

#### FACTORY

