KERN WTB 10K-3N



Ideal for food industry, thanks to its IP65 protection and special checkweighing display



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	IP protected bench scale
Product family	WTB

Measuring System	
Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	15000 g
Readability [d]	2 g
Resolution	7.500
Linearity	± 4 g
Reproducibility	2 g
Tare range	-14998 g
Default unit	g
Units	g
Units (if device is conformity assessed)	g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (M1)
Stabilization time	2 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	10 g
Maximum creep (15 minutes)	8 g
Maximum creep (30 minutes)	16 g
Loadcell type	aluminium IP65 silicone- coated

d special checkweighing	
Approval	
CE mark	✓
Display	
Display type	LCD
Display backlight	✓
Display digit height	25 mm
Construction	
Dimension housing (W×D×H)	286×316×126,5 mm
Dimensions completely mounted (W×D×H)	286×316×126,5 mm
Material housing	plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	263×203 mm
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓
Functions	
Auto-off interval(s) in mains power mode	3 min off 5 min 15 min
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 15 min
-	1.7. 1.15

manual (multi)

acoustically

visual

None

Tare function

Tolerance weighing

Underfloor weighing

Tolerance weighing - type of signal

1

KERN WTB 10K-3N



Ideal for food industry, thanks to its IP65 protection and special checkweighing display

Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	30 h
Rechargeable battery operating time - backlight off	50 h
Battery	no battery

Environmental conditions	
Humity of environment [Min]	0 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	400×340×200 mm
Net weight	3,2 kg
Shipping method	Parcel service
Net weight approx.	3,2 kg
Gross weight approx.	4,0 kg
Shipping weight	5,4 kg

Services (optional)	
Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

ACCU +3 DAYS