

# TECHNICAL DATA SHEET

jo\_CHAMP Compo Low ESD S3S No. 12371

Sz. 35 - 47



## LABELLING ACCORDING TO STANDARD

### FORM

Safety shoe



Form A - in size 42, the upper height must not exceed 11.2 cm.

## AREAS OF APPLICATION

Areas of application

Areas where there is a risk of electrostatic discharge (ESDS/ESD)

## FEATURES

ESD equipment

Thanks to its excellent discharge capability, the shoe is suitable for work in ESD sensitive or electrostatically protected areas (EPA). The shoes comply to the standard 61340-5-1.



Sizes (unisex model)

- Expanded size range: available in sizes 35 - 47

Certification in accordance with DGUV rule 112-191

- Certified for orthopaedic inserts



Full, padded bellows tongue

- Excellent wearing comfort: The tongue prevents pressure marks and avoids dirt from entering into the shoe.



Collar padding

- Excellent wearing comfort: the ankle-wrapping, softly padded upper edge provides for stability and grip in the shoe.

Reflective material

- Good visibility in the dark



<b>FEATURES</b>	
Metalfree equipment	<ul style="list-style-type: none"> <li>• Low weight</li> <li>• Suitable for work areas sensitive to metal</li> <li>• Does not trigger metal detectors</li> <li>• Use around induction loops is possible</li> </ul>
PU scuff cap (polyurethane)	<ul style="list-style-type: none"> <li>• Directly applied tip protection</li> <li>• Excellent wear protection in the shoe tip area</li> <li>• Protects the upper material in this area against premature wear</li> </ul>
<b>UPPER MATERIAL</b>	
Cowhide leather	<ul style="list-style-type: none"> <li>• Areas of application S1/S2/S3</li> <li>• Natural material</li> <li>• Wear-resistant</li> <li>• Breathable</li> <li>• Water penetration/absorption in accordance with EN ISO 20345 S2</li> </ul>
<b>LINING</b>	
Breathable fabric lining	<ul style="list-style-type: none"> <li>• Climate-regulating</li> <li>• Good ventilation</li> <li>• Skin-friendly</li> <li>• High absorption and emission of moisture</li> </ul>
Heel pocket lining	<ul style="list-style-type: none"> <li>• The abrasion-resistant microfibre material is particularly sturdy and provides for a pleasant wearing comfort.</li> </ul>
<b>TOE PROTECTION CAP</b>	
Composite toe cap 	<ul style="list-style-type: none"> <li>• Protection against impacts of min. 200 joules and pressure loading of min. 15 kN</li> <li>• Permanent edge coverage for cushioning</li> <li>• Ergonomically shaped</li> <li>• Comfortable toe room</li> <li>• Good coverage of the little toe area</li> <li>• Low weight - weighs less than conventional steel caps</li> <li>• 100% metal-free</li> <li>• 100% anti-magnetic</li> </ul>
<b>INLAY SOLE</b>	
Full-length inlay sole JORI TITAN 	<ul style="list-style-type: none"> <li>• ESD EQUIPMENT: Protection against electrostatic discharge (ESD). The full-length, exchangeable inlay sole is conductive and designed for the use in ESD safety footwear according to the standards DIN EN ISO 20345 and DIN EN 61340-5-1.</li> <li>• The full-length, exchangeable inlay sole provides the highest possible comfort in safety shoes.</li> <li>• The inlay sole is functionally absorbing and releasing moisture and thus provides for a pleasant foot climate.</li> </ul>

## PENETRATION RESISTANCE

Metal-free penetration protection with recycled material content

The textile midsole complies with the penetration safety standard EN 12568 and furthermore fulfils the additional requirements for penetration protection in accordance with EN ISO 20344 / 20345. The light and flexible material enables an increased elasticity of the shoe, which can particularly be recognized when working on uneven grounds or on your knees.

The textile variant offers 100 % foot coverage compared to steel midsoles (foot coverage 85 % due to limits in the shoe manufacturing process). Being 100 % metal-free and antimagnetic, this equipment is used as penetration protection in safety shoes.

The metal-free midsole (penetration protection) is made from 20% recycled polyester.

## OUTSOLE

jo\_EXPLORE double-density sole with profile



- Excellent slip resistance
- Antistatic

Outsole: PU (polyurethane)

- Colour: lightgrey
- Profile depth: 5,5 mm
- Abrasion-resistant
- Heat-resistant to approx. 130°C
- Flexible at cold temperatures to approx. -20°C
- Oil and fuel resistant

Midsole: PU (polyurethane)

- The soft PU core provides a good impact absorption and high wearing comfort