## KERN TB 2000-0.1F



Practical measuring device for measuring the thickness of layers for daily use



| Category          |                                    |
|-------------------|------------------------------------|
| Brand             | Sauter                             |
| Product categoriy | Coating thickness measuring device |
| Product group     | Digital coating thickness gauge    |
| Product family    | TB                                 |

| Measuring System                                 |  |
|--|--|
| Units  | μm<br>inch (mil)                             |
| Tolerance (% of [Max])                           | 3%   |
| Readability coating thickness [d] (µm)           | 0,1 μm; 1 μm                                 |
| Minimum thickness coating                        | 300 μm                                       |
| Measuring range coating thickness [d] ( $\mu$ m) | 100 μm; 2000 μm                              |
| Offset accur (% of [Max])                        | 1%   |
| Sensor placement position                        | external                                     |
| Coating thickness gauge sensor type              | FE   |
| Test object thickness coating                    | Non-magnetic coatings on iron, steel, Type F |
| Smallest sample, flat [radius]                   | 6 mm   |
| Smallest sample, concave [radius]                | 25 mm  |
| Smallest sample, convex [radius]                 | 1,5 mm                                       |

| Approval |   |  |
|----------|---|--|
| CE mark  | ✓ |  |
| Display  |   |  |

Display type

LCD

| Dimension (W×D×H) 161×69×32 mm                     |
|--|
| Dimension housing (W×D×H) 161×69×32 mm             |
| Dimensions completely mounted (W×D×H) 161×69×32 mm |
| Material housing plastic                           |
| Cable length 1 m                                   |

| Functions                                 |   |
|---|---|
| Increase in measurement accuracy possible | ✓ |

| Power Supply               |                    |
|----------------------------|--------------------|
| Supplied power supply      | Battery            |
| Battery                    | 4×1.5 V AA         |
| Battery / accumulator type | Alkali(-Manganese) |
| Battery capacity           | 2.600 mAh          |
| Battery voltage            | 1,5 V              |

| Environmental conditions  |        |
|---------------------------|--------|
| Ambient temperature [Min] | -10 °C |
| Ambient temperature [Max] | 40 °C  |
| Storage temperature [Min] | -10 °C |
| Storage temperature [Max] | 40 °C  |

| Packing & Shipping           |                |
|------------------------------|----------------|
| Readability force [d] (N)    | 1 d            |
| Dimensions packaging (W×D×H) | 265×215×71 mm  |
| Net weight                   | 0,26 kg        |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,30 kg        |
| Gross weight approx.         | 0,75 kg        |
| Shipping weight              | 0,8 kg         |

| Services (optional)                    |         |
|--|---------|
| Article number for factory calibration | 961-110 |

1

## KERN TB 2000-0.1F



Practical measuring device for measuring the thickness of layers for daily use

## Pictograms

**STANDARD** 









**OPTION** 

