

KERN TF 1250-0.1FN



Premium coating thickness gauge for paint layer, lacquer layer etc.



Approval

CE mark	✓
---------	---

Display

Display type	LCD graphic
Display digit height	10 mm

Construction

Dimension (W×D×H)	126×65×35 mm
Dimension housing (W×D×H)	126×65×35 mm
Dimensions completely mounted (W×D×H)	126×65×35 mm
Material housing	plastic

Functions

Statistic function	✓
Continuous capture possible	✓
Memory function	✓
Increase in measurement accuracy possible	✓

Power Supply

Supplied power supply	Battery
Battery	2×1.5 V AAA
Battery / accumulator type	Alkali(-Manganese)
Battery capacity	1.100 mAh
Battery voltage	1,5 V
Battery operating time	50 h

Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	50 °C
Storage temperature [Min]	0 °C
Storage temperature [Max]	50 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	260×220×70 mm
Net weight	0,083 kg
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,85 kg
Shipping weight	0,82 kg

Category

Brand	Sauter
Product category	Coating thickness measuring device
Product group	Digital coating thickness gauge
Product family	TF

Measuring System

Units	µm inch (mil)
Tolerance (% of [Max])	3%
Readability coating thickness [d] (µm)	0,1 µm; 1 µm
Minimum thickness coating	300 µm
Measuring range coating thickness [d] (µm)	100 µm; 1250 µm
Offset accur (% of [Max])	1%
Sensor placement position	internal
Coating thickness gauge sensor type	FE NFE
Test object thickness coating	Non-magnetic coatings on iron, steel, Type F Coatings on non-magnetic metals, type N
Smallest sample, flat [radius]	13 mm
Smallest sample, concave [radius]	80 mm
Smallest sample, convex [radius]	1,5 mm
Internal data memory: Number of value groups	1
Internal data memory: Number of individual values	99

KERN TF 1250-0.1FN



Premium coating thickness gauge for paint layer, lacquer layer etc.

Services (optional)

Article number for factory calibration	961-112
--	---------

Pictograms

STANDARD



OPTION

