



WEPBA 20-125 Quick DS BL

- Compact 2000 Watt angle grinder for industrial use: with Brushless motor for maximum productivity and unrivalled service life
- Highly efficient, service-free Marathon Brushless motor: patented cooling and innovative dust protection for triple service life compared to brush motors
- Tacho Constamatic (TC) Electronics: extremely fast work progress thanks to high speed even under load
- Tool free, fast disc change at the touch of a button with the Metabo M-Quick-System
- Tool-free adjustable guard; twist-proof
- Low-vibration side handle Metabo VibraTech (MVT)
- Best anti-vibration system: integrated auto-balancer for up to 50% less hand-arm vibrations, longer service life of the machine and up to twice the service life of the grinding wheels
- Best ratio of performance to handle circumference on the market for low-fatigue working
- Paddle switch with dead man function: safe to operate due to an ergonomically integrated non-slip switch
- Highest level of user safety thanks to fast brake, anti-kickback, overload protection, soft start and restart protection
- Gear housing can be unscrewed, rotated in 90° steps and re-mounted for left-handed operation or cutting
- Particularly easy servicing thanks to cable replacement cover
- Detachable dust filter protects motor from coarse particles
- Steel ring to accommodate the carabiner secures the angle grinder against falling when working at great heights

Order no.	600643000
EAN code	4061792207165
Disc-Ø	125 mm // 5 "
Rated input power	2000 W
Output power	1600 W
No-load speed	11000 rpm
Spindle thread	M 14
Weight (without power cable)	2.6 kg / 5.7 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Clip for cut-off guard, Inner support flange, M-Quick flange nut, Metabo VibraTech (MVT) side handle, Dust protection filter