



## LF 850 S

- The original from Metabo: the problem solver for renovation work. Saves up to 70% of time when compared to conventional working methods
- For the environmentally-friendly removal of paint and varnish from even wooden surfaces, such as stairs, doors and windows
- Suitable for processing untreated wood
- Suitable for processing notches by virtue of lateral blades
- Variably adjustable milling depth
- Die cast aluminium gear housing for optimum heat dissipation and durability
- Carbide reversible blade, can be used on four sides for a long service life
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- With metaBOX, the intelligent solution for transport and storage

Order no.	601049500
EAN code	4061792258020
Torque	2 Nm / 18 in-lbs
Cutting edge cycle	80 mm / 3 1/8 "
Maximum notch depth	unlimited
Lateral milling height	28 mm / 1 1/8 "
Axial routing depth	0 - 0.3 mm // 0 - 0.012 "
Radial routing depth	0.15 mm / 0.006 "
Rated input power	850 W
Output power	470 W
No-load speed	11500 rpm
Speed at rated load	7500 rpm
Weight (without power cable)	2.5 kg / 5.5 lbs
Cable length	4 m / 13.12 ft

### Scope of delivery

4 Carbide reversible blades, Extraction connector, Adjusting wrench with handle, Combo-spanner, metaBOX 145