



## G 400

- Robust die grinder for deburring, milling, grinding and cutting, also in hard-to-reach places
- Long grinding spindle - ideal for working on hard to reach places
- Precise collar for stationary use
- Removable protective rubber cap for comfortable and safe working
- Slim design for ideal handling

<b>Order no.</b>	<b>601052000</b>
<b>EAN code</b>	<b>4061792257627</b>
No-load speed	30000 rpm
Rated input power	380 W
Output power	250 W
Speed at rated load	12400 rpm
Collar diameter	43 mm / 1 11/16 "
Collet chuck bore	6 mm / 0.2362 "
Weight (without power cable)	1.5 kg / 3.3 lbs
Cable length	2.55 m / 8 ft

### Scope of delivery

Collet 6 mm, Protective rubber cap, 2 Open-jawed spanners