



AS 36-18 L 20 PC with Manual Filter Cleaning

- Compact cordless vacuum cleaner of dust class L with integrated filter cleaning for versatile application
- Compact vacuum cleaner for liquids and dry solids with commercial registration
- User safety: certified in accordance with EU standard for dust class L
- PressClean: manual filter cleaning using strong air flow by activating the switch on the extraction unit during breaks
- Eco mode for longer runtime per battery pack charge, boost mode for maximum power
- Automatic trailing mechanism for emptying the suction hose completely
- Suction stop when vacuuming liquids once the maximum fill level is reached
- Basic antistatic equipment prevents static charge when using appropriate accessories
- Fast coupling of metaBOXes with tools and accessories on the vacuum cleaner for easy change of location
- Supplied vacuum cleaner accessories with quick system for fast retrofitting when in use
- Easy transport thanks to hose holder and storage for pipes and nozzles
- Dust-proof and splash-proof battery pack compartment with lockable flap
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no. EAN code	602071850 4061792230453
Battery voltage	18 V
Air output max.	3300 l/min / 117 cfm
Vacuum	140 hPa (mbar) / 2 psi
Filter surface	3500 cm ² / 542 sq.inch
Container volume	20 l / 5 gal
Suction hose Ø	32 mm / 1 1/4 "
Hose length	3.2 m / 10.5 ft
Weight without battery pack	9.2 kg / 20.3 lbs

Scope of delivery

Antistatic suction hose Quick (Ø 32 mm / 3.2 m), 3 Plastic suction tubes, Fleece filter bag, Suction nozzle (120 mm wide), Floor nozzle (300 mm wide), Crevice nozzle, Brush nozzle, Coupling bush Quick Ø 28/35 mm, Handle adapter Quick Professional, without battery pack, without charger