



SB 18 L BL

- Metabo's smallest 18 volt hammer drill with powerful brushless performance for all standard drilling and screwdriving applications
- Hammer drill function for drilling in masonry
- Extremely short and light hammer drill for comfortable handling even over head or in tight spaces
- Robust, durable gear housing made from aluminium die-cast
- Powerful Brushless motor for greatest efficiency and long battery pack runtime
- Overload protection: protects the motor from overheating
- Integrated LED work light with afterglow function for optimal brightness in the work area
- With handy belt hook and bit case which can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	613157840
EAN code	4061792245969
Battery voltage	18 V
Maximum torque, soft	28 Nm / 247.8 in-lbs
Maximum torque, hard	65 Nm / 575.3 in-lbs
Adjustable torque	0.5 - 9 Nm // 4.4 - 79.7 in-lbs
Drill-Ø masonry	13 mm / 1/2 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	40 mm / 1 9/16 "
No-load speed	0 - 500 / 0 - 1700 rpm
Maximum impact rate	25500 bpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	0.9 kg / 2 lbs

Scope of delivery

Keyless chuck, Belt hook and bit case, metaBOX 145, without battery pack, without charger