



## SB 18 L BL Q

- Metabo's smallest 18 volt hammer drill with powerful brushless performance for all standard drilling and screwdriving applications
- Hammer drill function for drilling in masonry
- Extremely short and light hammer drill for comfortable handling even over head or in tight spaces
- Metabo Quick System: quick change of bit retainer and bits, for flexible working
- Robust, durable gear housing made from aluminium die-cast
- Spindle with magnetic hexagon recess for screwdriver bits for working without chuck
- Powerful Brushless motor for greatest efficiency and long battery pack runtime
- Overload protection: protects the motor from overheating
- Integrated LED work light with afterglow function for optimal brightness in the work area
- With handy belt hook and bit case which can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

<b>Order no.</b>	<b>613158840</b>
<b>EAN code</b>	<b>4061792254602</b>
Battery voltage	18 V
Maximum torque, soft	28 Nm / 247.8 in-lbs
Maximum torque, hard	65 Nm / 575.3 in-lbs
Adjustable torque	0.5 Nm // 4.4 - 9 / 79.7 in-lbs
Drill-Ø masonry	13 mm / 1/2 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	40 / 1 9/16 "
No-load speed	0 - 500 / 0 - 1700 rpm
Maximum impact rate	25500 bpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	0.9 kg / 2.1 lbs

### Scope of delivery

Quick-change chuck, Belt hook and bit case, meta-BOX 145, without battery pack, without charger