



SBE 800-2

- Universal two-speed impact drill with variable speed for drilling into almost all materials
- Vario (V)-Electronics for working at customised speeds to suit various application materials
- Thumbwheel for Speed Preselection
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the tool stop unexpectedly
- Forward and reverse rotation
- Spindle with hexagonal recess for screwdriver bits for working without chuck

| Order no. | 601744510 |
|-------------------------------------|-----------------------------|
| EAN code | 4061792248250 |
| Rated input power | 800 W |
| Drill-Ø masonry | 20 mm / 25/32 " |
| Drill-Ø concrete | 18 mm / 23/32 " |
| Drill Ø steel | 13 / 8 mm // 1/2 / 5/16 " |
| Drill-Ø soft wood | 40 / 25 mm // 1 9/16 / 1 " |
| No-load speed | 0 - 1200 / 0 - 3200 rpm |
| Speed at rated load | 850 / 2200 rpm |
| Maximum impact rate | 51200 bpm |
| Gears | 2 |
| Chuck capacity | 1.5 - 13 mm // 1/16 - 1/2 " |
| Collar diameter | 43 mm / 1 11/16 " |
| Drill spindle with hexagonal recess | 6.35 mm / 1/4 " |
| Drill spindle thread | 1/2 " - 20 UNF |
| Chuck clamping type | Geared Chucks |
| Weight (without power cable) | 2.3 kg |
| Cable length | 4.1 m |

Scope of delivery

Geared Chucks, Chuck Keys, Side handle, Drilling depth guide, Plastic carry case