



## Novorapid 115 x 1.6 x 22.23 mm, Inox, cutting disc, straight type

- Quality Novorapid: powerful entry-level class
- Thin cutting disc for processing rust-free, thin-walled materials such as pipes, sheeting, profiles, wires etc. as well as for general metal processing
- Good cutting performance with good tool life.
- Hardness: hard
- Low material consumption, power-saving, low machine load
- Low in iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %)
- Maximum working speed: 80 m/s

Order no.	616315000
EAN code	4061792252806
Quality class	A 46-T
Diameter x thickness x bore	115 x 1.6 x 22.23 mm
Version	straight
Maximum speed	13200 rpm
Sales unit / packaging unit	1 / 25