



TBP 6200/8 Inox

- Powerful, slim deep well pump for pumping up to 6,200 litres of clear water per hour from wells and shafts
- Powerful and quiet pump running gear with 8 gears for particularly high delivery rate
- Slim design for use in drilled wells from Ø 100 mm (4")
- Robust stainless steel housing and high-quality components for extremely long service life
- Maintenance-free motor for efficient, economical operation
- Overload protection: automatic shutdown if overheating is imminent, after cooling down the pump starts automatically
- Integrated check valve prevents dry running of the pump when it is switched off, enabling a short restart process
- Integrated filter and high-quality mechanical seal for reliable function, even in continuous mode
- Base for safe operation on the ground, removal optional for operation in a drilled well
- Comfortable installation thanks to practical eyelets on the pump head for the lowering cable

Order no.	61021700
EAN code	4061792254503
Rated input power	1100 W
Maximum delivery rate	6200 l/h / 1638 gal/h
Maximum delivery height	55 m / 180 ft
Maximum pressure	5.5 bar / 79 psi
Maximum immersion depth	19 m / 62 ft
Discharge port	1 1/4" female thread
Pump housing	Stainless steel
Pump diameter	98 mm
Protection type IP	IP X8
Number of impellers	8
Dimensions	124 x 124 x 816 mm // 4.882 x 4.882 x 32.126 "
Weight	9.3 kg / 20.5 lbs
Cable length	22 m / 72 ft

Scope of delivery

Base, Lowering cable, Screwdriver