

ASM 18-3 PC

Precision cordless screwdriver, mid-mounted handle, up to 3 Nm

Parameterisable cordless screwdriver with mechanical shut-off clutch for industrial use.

Part number: 7 112 77 60 00 0



FEIN benefits

- › Process-capable according to ISO 5393, VDI/VDE 2647, achieves CMK value > 1.67 at $\pm 10\%$ (refers to 6 Sigma).
- › For soft and hard screwed connections.
- › Programmable parameters (up to 5 steps): speed, direction of rotation, angle of rotation, torque threshold, time.
- › Error criteria settings can prevent manipulation of the screwdriving process.
- › Infinitely variable speed adjustment.
- › Parameters can be set for forwards or reverse running.
- › Brushless motor with 30% higher efficiency and long service life.
- › High speed stability for constant work progress.
- › Can be fully loaded up to maximum output torque during continuous operation.
- › Extra short design for use in tight spaces.
- › Fatigue-free working thanks to narrow grip dimensions and good balance.
- › Optimised air guide: air isn't blown onto the user's hand or into his or her face.
- › Extra large and bright signal unit (OK / not OK).
- › Optimum illumination of the screwdriving site.
- › Wear-free acceleration switch.
- › Tools can be colour-coded using coding rings.
- › Scope for attaching suspension bracket (balancer).
- › Integrated fastening counter means that a maintenance interval can be set.
- › Adjustable battery charge state display on tool.
- › MultiVolt interface. Cordless tool can be operated with all FEIN Li-ion batteries (12-18 V).

Supplied

- ✓ Supplied without battery, charger or torque wrench.



Technical data

GENERAL TECHNICAL DATA

Battery voltage

18 V

Battery interface

MultiVolt

Torque range

0.5 - 3 Nm

Speed, no load

110 - 1,200 rpm

Tool Holder

1/4 in hexagon socket

Weight without storage battery

0.80 kg