

430-028 Parallel clamp with double spindle guidance, clamping range up to 28 mm, 16 mm clamping depth



DESCRIPTION

The parallel clamps of the series 430 are used thanks to their double spindle guide for the precise, parallel adjustment of the clamping surfaces in craftsmanship, industry, and workshop.

RANGE OF APPLICATION

Thanks to their double spindle guide for precise, parallel adjustment of the clamping surfaces

BENEFIT

- Clamping force up to 4,000 N
- Smooth-running spindles ensure even greater force transmission
- Numerous variants of clamping range and clamping depth of clamps enable the holding of parts of different sizes

OPERATION

- Apply the clamp to the workpiece to be held and adjust through spindle guidance
- Tighten the threaded spindle to fix the workpiece firmly

MASTER DATA

GTIN [EAN]	4027474606084
Country of origin	DE
Case material	Tool steel
Series	430
Net weight [kg]	0,14 kg
Package contents	1 piece
Packaging Act	PP 05
Global sales capability given	Yes (REACH, RoHS, POP, PROP65, TSCA)

APPLICATION IMAGE

