

480K1000-175 All-steel construction clamp with tommy handle, max. 1.000 mm clamping range, 175 mm clamping depth



RANGE OF APPLICATION

For extra heavy and severe stress when clamping workpieces in steel construction, locksmith's shops, commercial vehicle construction, mechanical engineering, etc

BENEFIT

- Clamping force up to 22,000 N
- Movable special pressure cap allows clamping of angled workpieces up to 35°
- Hexagon allows the use of key, ratchet or impact wrench
- Smooth-running trapezoidal spindles ensure even higher power transmission.

OPERATION

- Place the fixed arm against the workpiece to be held and roughly fix it by moving the sliding arm
- Tighten the spindle by operating the handle to firmly fix the workpiece in place

MASTER DATA

GTIN [EAN]	4027474033958
Country of origin	DE
Case material	Tool steel
Series	480K
Net weight [kg]	9,245 kg
Package contents	1 piece
Packaging Act	PP 05
Global sales capability given	Yes (REACH, RoHS, POP, PROP65, TSCA)