


# 128-F-SW 2-jaw universal puller, up to 60 mm clamping range, 50 mm clamping depth



APPLICATION IMAGE



## DESCRIPTION

The 2-jaw universal wiper puller is used for pulling off stuck, rusted, and deeply embedded wiper arms on windshields and rear windows. The pressure piece on the spindle ensures the perfect contact surface and guarantees gentle pulling.

## RANGE OF APPLICATION

For pulling off stuck, rusted and recessed windscreen wiper arms on windcreens and rear windows

## BENEFIT

- Especially gentle pulling thanks to the special pressure piece on the spindle
- Anti-slip device at the spindle head for safe work with a wrench
- Spindle outlet to protect the thread

## OPERATION

- Position the puller leg from the outside onto the wiper arm
- Slide the claws under the component
- Use a wrench to secure the hooks
- Manually pull the spindle to apply pressure
- Move the hexagon drive (male) on the spindle head with a ratchet or ring spanner until the component is released

## MASTER DATA

GTIN [EAN]	4021176971242
Country of origin	DE
Case material	Tool steel
Series	128-F
Net weight [kg]	0,245 kg
Package contents	1 piece
Packaging Act	PAP 21
Global sales capability given	Yes (REACH, RoHS, POP, PROP65, TSCA)

## SPARE PARTS

- 128-DS-36\_Pressure piece for 128-T-4
- 128-F-SW17\_Pressure piece
- 128-FSW-50-P\_2 replacement jaws (pair)
- 128-SW06\_Press spindle
- 610060\_Press spindle