



KH 18 LTX BL 35 Q with Metabo Quick change chuck

- Metabo's strongest SDS-plus cordless hammer for quick drilling and efficient chiseling in concrete and masonry
- Maximum drill performance, efficiency and service life thanks to brushless technology and high-performance hammer action
- Combination hammer with 3 functions: hammer drilling, drilling and chiselling
- Metabo VibraTech (MVT): integrated damping system to reduce vibrations in order to protect the user's health
- Perfect ergonomics thanks to the centre of gravity being near the hand and optimised handle contour
- Metabo Quick: quick change between SDS Plus hammer chuck and keyless chuck for many different applications
- Can be switched to anticlockwise rotation to easily loosen tilted tool attachments
- Optional reduction of speed and impact energy for starting a drill hole or working in softer materials
- Restart protection: prevents unintentional start-up after battery pack change
- Double safety when the drill bit jams: No kick-back thanks to the mechanic decoupling plus ultra-fast sensor-controlled shutdown
- LED work light for optimum view of the drilling site
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	600813660
EAN code	4061792264229
Type of battery pack	LiHD
Battery voltage	18 V
Battery pack capacity	2 x 5.5 Ah
Max. single blow energy (EP-TA)	4.2 J
Maximum impact rate	4350 bpm
Drill-Ø concrete with hammer drills	32 mm / 1 1/4 "
No-load speed	0 - 810 rpm
Bit retainer	SDS-plus
Weight without battery pack	4.4 kg / 9.7 lbs
Weight with battery pack	5.4 kg / 11.9 lbs

Scope of delivery

Hammer chuck for tools with SDS-plus shank end, Keyless chuck for tools with cylindrical shank, Side handle, Drilling depth guide, 2 LiHD battery packs (18 V/5.5 Ah), Quick charger ASC 145 "AIR COOLED", metaBOX 185 XL