

971-241 Circular pattern snips 243 mm, links, with lever transmission (light design)



DESCRIPTION

The circular pattern snips in the light version are used for curved cuts as well as short and straight cuts. The legs of the snips are made of sturdy sheet steel and are equipped with an anti-slip 2-component coating. The built-in opening spring guarantees easy handling and operation. The maximum cutting performance ranges from 1.0 mm for V2A sheets to 1.2 mm for sheets. Thanks to the optimized design and geometry of the snips, even hard-to-reach areas can be accessed.

RANGE OF APPLICATION

For curved cuts as well as short and straight cuts

BENEFIT

- High force through force-amplifying lever
- Ergonomic handle for fatigue-free working
- Bent shape available in right- or left-cutting

OPERATION

- Place the sheet metal at the opened scissor head
- Move the scissor arms up and down until the sheet metal is cut

MASTER DATA

GTIN [EAN]	4027474557232
Country of origin	DE
Case material	Tool steel
Series	971
Net weight [kg]	0,38 kg
Package contents	6 piece
Packaging Act	PP 05
Global sales capability given	Yes (REACH, RoHS, POP, PROP65, TSCA)