

626400 Mechanical pressure spindle Ø 26,441 mm for spindle thread G 3/4" / 14, 400 mm length, 5,4 mm thread



DESCRIPTION

The mechanical spindle is the heart of every KUKKO puller. It allows a maximum tension force of 10 t to be achieved. The manual actuation of the spindle ensures sensitive control of the pulling process. The fine thread also guarantees perfect power transmission. A reversible spindle tip enables safe placement of the spindle on both smooth surfaces and centering points.

RANGE OF APPLICATION

For a sensitive control of the Pulling process and perfect power transmission.

BENEFIT

- Optimal sliding properties in the thread thanks to special coating
- Ideal adjustment of the spindle to the shaft through double-sided spindle tip
- Bearing-mounted, freely rotating centring tip protects the shaft from damage when applying pulling force
- Extremely durable due to rolled threads
- Including KUKKO special grease

MASTER DATA

GTIN [EAN]	4021176125423
Country of origin	DE
Case material	Tool steel
Series	6
Net weight [kg]	1,66 kg
Package contents	1 piece
Packaging Act	PP 05
Global sales capability given	Yes (REACH, RoHS, POP, PROP65, TSCA)