

Product data sheet

610 084 3 2

Ferrule crimping tool PEW 8.84

Sideways insertion



- For crimping insulated and non-insulated ferrules according to DIN 46 228
- Self-adjusting adaptation to the required size of ferrule
- Ferrules are inserted sideways into the tool
- Force magnified by lever action to ensure fatigue-free working
- Precise, factory-set (calibrated) crimping pressure
- Consistent crimping quality with forced-lock completion of crimping process (can be released)
- 2 profiled/2 smooth crimp surfaces
- Black-oxide finish
- Specially hardened spring steel
- Ergonomic 2-component grips

General

Article Number	610 084 3 2
EAN	4049002018145
Weight	440 g
Dimension	180 mm
Dimension packaging	250 x 108 x 43 mm

Specifications

Finish	black-oxide finish
Grips	2-component grips
Range of applications	Ferrules
Capacity	0.08 – 10.0 mm ² / AWG 28 – 8
Twin ferrules	2x 0.25 – 6.0 mm ² / 2x AWG 22 – 8

Classification

eCl@ss 10.1	ACD215012
ETIM 7.0	EC000168
proficl@ss 7.0	AAA946c003

With reservations regarding technical modifications and errors. Illustration may vary.