



SB 18 L

- Reliable, powerful hammer drill for all standard drilling and screwdriving applications
- Hammer drill function for drilling in masonry
- Overload protection: protects the motor from overheating
- Integrated LED work light with afterglow function for optimal brightness in the work area
- With handy belt hook and bit case which can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	614053500
EAN code	4061792245242
Type of battery pack	LiPOWER
Battery voltage	18 V
Battery pack capacity	2 x 2 Ah
Maximum torque, soft	26 Nm / 230 in-lbs
Maximum torque, hard	60 Nm / 531 in-lbs
Adjustable torque	0.7 - 5.5 Nm // 6.2 - 48.7 in-lbs
Drill-Ø masonry	13 mm / 1/2 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	36 mm / 1 13/32 "
No-load speed	0 - 450 / 0 - 1850 rpm
Maximum impact rate	28500 bpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	1.2 kg / 2.6 lbs
Weight with battery pack	1.6 kg / 3.5 lbs

Scope of delivery

Keyless chuck, Belt hook and bit case, 2 LiPOWER Battery Packs (18 V/2.0 Ah), Charger SC 36, metaBOX 145