

Click-Torque Lock A 6 R/L Torque wrench, adjustable, Torque Lock function,
continuous bit mounting (1/4"), 2.5-25 Nm, 1/4" x 2.5-25 Nm
Click-Torque Lock R/L series - adjustable torque wrenches with Torque Lock function



EAN:	4013288233653	Size:	330x50x50 mm
Part number:	05075694001	Weight:	592 g
Article number:	Click-Torque Lock A 6 R/L	Country of origin:	TW
		Customs tariff number:	82041100

- For clockwise and counterclockwise operation
- Torque Lock function: The torque function can be deactivated so that the tool can also be used for loosening
- With continuous bit mounting (1/4") for controlled clockwise and counterclockwise torque operation
- Extra click: audible and tactile torque setting
- Torque wrench gives an audible and tactile signal
- Measuring range: 2.5-25 Nm; precision $\pm 4\%$ as per DIN EN ISO 6789-1:2017-07

Adjustable torque wrench for controlled clockwise and counterclockwise torque operation. With continuous external hexagon mounting for 1/4" hex drive bits (bits can be inserted from both sides of the torque wrench). Also suitable for 1/4" sockets with the 870/1 adapter (05136000001). The torque function can be deactivated (Torque Lock function), so that the tool can also be used for loosening. Easy setting and saving of the default value. The audible and tactile clicks on reaching the scale values facilitate the safe setting of the desired torque value. The robust release mechanism guarantees a clearly audible and tactile release signal when the set torque value is reached. Fine-toothed reversible ratchet with 45 teeth. Accuracy of $\pm 4\%$ as per DIN EN ISO 6789-1:2017-07.



Web link

https://products.wera.de/en/new_products_2025_click-torque_lock_series_-_adjustable_torque_wrenches_with_torque_lock_function_click-torque_lock_r_l_series_-_adjustable

Wera - Click-Torque Lock A 6 R/L
05075694001 - 4013288233653

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Click-Torque Lock A 6 R/L Torque wrench, adjustable, Torque Lock function,
 continuous bit mounting (1/4"), 2.5-25 Nm, 1/4" x 2.5-25 Nm
 Click-Torque Lock R/L series - adjustable torque wrenches with Torque Lock function



For 1/4" hex drive bits

Torque Lock function

Exact



Click-Torque A 6



The continuous bit mounting (bits can be inserted from both sides of the torque wrench) is suitable for all 1/4" bits as per ISO 1173.



The torque function can be deactivated so that the tool can also be used for loosening.




Precision of ±34 % as per DIN EN ISO 6789-1:2017-07.

Easy and safe

Setting with Speed

Release mechanism



Easy setting and saving of the desired torque value; easy to read on main and fine scales.



With audible and tactile locking when the scale values are reached.



On reaching the desired torque value, an audible and tactile mechanism is triggered.

Further versions in this product family:

	inch	Nm	Nm	lbf. ft.	mm	mm	mm	mm	mm	inch	inch	inch	inch	inch
05075694001 ¹⁾	1/4"	0.10	2.5-25	1-18	299	123	42	26	11.75	11 49/64"	4 53/64"	1 41/64"	1 1/64"	29/64"

1) Available from September 2025

Web link

https://products.wera.de/en/new_products_2025_click-torque_lock_series_-_adjustable_torque_wrenches_with_torque_lock_function_click-torque_lock_r_l_series_-_adjustable

Wera - Click-Torque Lock A 6 R/L
 05075694001 - 4013288233653

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de