

Torque insert for Pull studs to DIN 69872, suitable for steep tapers: 40 SK



Order data

Order number	308810 40
GTIN	2050001771629
Item class	39Z

Description

Version:

Base, lever arm, and catch of cast steel, pin of hardened steel. **For high retaining force.**

Advantage:

Unlike conventional clamping wrenches it cannot slip, no risk of injury!

Application:

For safe tightening of pull studs.

suitable for pull studs with colour code: SK 40

Plug-in shank: 9×12 mm

Technical description

Plug-in shank	9×12 mm
suitable for pull studs with colour code	SK 40
suitable for steep tapers	40

Accessories

Torque wrench base unit without plug-in head maximum torque 60 N·m	656055 60
Torque wrench base unit with adjustment scale maximum torque 50 N·m	657277 50
QuickSelect torque wrench with adjustment locking, without plug-in head Maximum torque 50 N·m	657099 50
Torque wrench base unit without plug-in head maximum torque 60 N·m	656510 60
Torque wrench QuickSelect without plug-in head maximum torque 50 N·m	657094 50
Torque wrench base unit without scale without plug-in head maximum torque 50 N·m	657450 50
Deflecting torque wrench without scale maximum torque 60 N·m	657750 60
Torque wrench base unit maximum torque 80 N·m	657500 80
Torque wrench base unit maximum torque 100 N·m	657410 100