

Garant**KNUX 160410L, Grade: HB7020**

Order data

Order number	251038 HB7020
GTIN	4045197711175
Item class	21G

Technical description

Corner radius	1 mm
Chip breaker	SM
Main application	P
Chip diverter	2.2 mm
Cutting depth a_p	0.5 - 5 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting conditions	slightly interrupted
Grade	HB7020
Cutting speed v_c main application	120 - 350 m/min
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160410L
Type of product	Indexable insert for turning

