

Garant
KNUX 160405L, Grade: HB7020

Order data

Order number	251072 HB7020
GTIN	4045197711298
Item class	21G

Description

KNUX 160405L HB7020 Grade: HB7020

Chip breaker: SG

Chip diverter: 3.2 mm

 Cutting depth a_p : 1 - 6 mm

 Feed f : 0.2 - 0.5 mm/rev.

 Cutting speed v_c main application: 100 - 375 m/min

Technical description

Main application	P
Corner radius	0.5 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	1 - 6 mm
Chip diverter	3.2 mm
Chip breaker	SG
Cutting conditions	slightly interrupted
Grade	HB7020
Cutting speed v_c main application	100 - 375 m/min
Finishing/roughing assignment	Roughing

Tool material	Carbide
Number of changes/inserts	2
ISO code indexable insert	KNUX 160405L
Type of product	Indexable insert for turning