



Copy mill extra long, Plain shank, Ø D: 16_ mm

Order data

Order number	212606 16_
GTIN	4045197711823
Item class	210

Description

Version:

Exactly accurate insert bedding due to optimised design of insert and insert seat tolerances. Highest interchange accuracy guaranteed: ± 0.015 mm.

Description:

Highly accurate insert bedding due to optimised insert seat tolerances. Improved protection of indexable inserts. For finishing operations in tool and mould making.

Application:

General use for finishing and semi-finishing operations.

Steel – for general use in machining drop-forgings, and in tool and mould making.

Note:

Calculate the speed based on the effective $\varnothing D_w$.

Milling application: Copy milling

Tool exchange: PowerCard

Technical description

Direction of infeed	
Machining strategy	
Milling application	Copy milling
Milling head suitable for insert shape	
Shank type	Plain shank
Tool exchange	PowerCard
Spacing of the cutters	
Setting angle κ	
Type of product	

