

Garant
Copy mill short, Plain shank, Ø D: 32mm

Order data

Order number	212601 32
GTIN	4045197712677
Item class	210

Description
Version:

Exactly accurate insert bedding due to optimised design of insert and insert seat tolerances. Highest interchange accuracy guaranteed: ± 0.015 mm.

Application:

General use for finishing and semi-finishing operations.

Steel – for general use in machining drop-forgings, and in tool and mould making.

Note:

Calculate the speed based on the effective $\varnothing D_w$.

Technical description

Cutting edge $\varnothing D_c$	32 mm
Insert screw	219876 (30IP. 6.0 Nm)
$\varnothing d_1$	27 mm
Overall length L_{tot}	186 mm
Shank $\varnothing D_s$ h6	32 mm
Overhang L_1	100 mm
Number of cutting edges Z	2
Through-coolant	yes
Shank type	Plain shank
Milling application	Copy milling

Tool exchange	PowerCard
Type of product	Copy mill

Accessories

Clamping screw	219876
----------------	--------