



GÜNZBURGER STEIGTECHNIK

Aluminium work platform with steel grid, Number of steps including platform: 2



Order data

Order number	966149 2
GTIN	4031405510180
Item class	98G

Description

Version:

Sturdy welded tubular design, steps of non-slip steel grid. Stile ends with non-slip plastic end caps. Mobile by means of 2 lift rollers. Upper standing area 550 × 300 mm.

Technical description

Weight	8 kg
Footprint depth	0.73 m
Footprint width	0.69 m
Platform depth	300 mm
Platform height without railing	0.4 m
Accessibility	single-sided
Rollers	yes
Platform width	550 mm
Material	welded tubular design, steps of non-slip steel grid.

Type of step	Step
Working height approx.	2.4 m
Number of steps including platform	2
Ladders and platforms load capacity	150 kg
Type of product	Work platform