

**Garant****Copy mill short, Plain shank, Ø D: 10mm****Order data**

Order number	212601 10
GTIN	4045197712622
Item class	210

**Description****Version:**

Exactly accurate insert bedding due to optimised design of insert and insert seat tolerances.  
Highest interchange accuracy guaranteed:  $\pm 0.015$  mm.

**Application:**

General use for finishing and semi-finishing operations.

**Steel** – for general use in machining drop-forgings, and in tool and mould making.

**Note:**

Calculate the speed based on the effective  $\varnothing D_w$ . Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

**Technical description**

Cutting edge $\varnothing D_c$	10 mm
Overall length $L_{tot}$	92 mm
Overhang $L_1$	32 mm
$\varnothing d_1$	8 mm
Shank $\varnothing D_s$ h6	12 mm
Insert screw	219871 (8IP; 1.2 Nm)
Number of cutting edges Z	2
Through-coolant	yes
Shank type	Plain shank

Milling application	Copy milling
Tool exchange	PowerCard
Type of product	Copy mill

---

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Clamping screw	219871
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2