

HOLEX

Face mill arbor with cooling channel bore, HSK-A 100 short, Spigot \varnothing d1: 22mm



Order data

Order number	306677 22
GTIN	4045197712318
Item class	32A

Description

Version:

- Clamping \varnothing 40 with 4 tapped holes for drive blocks to DIN 2079.
- With Balluff/RFID chip bore.
- Increased collar contact surface.
- HSK mating faces machined.

With **cooling channel bores.**

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

Technical description

Overhang dimension A	50 mm
Milling mandrel length L_4	19 mm
Spare milling cutter lock screw No. 309860 / 309861	22
Spigot \varnothing d ₁	22 mm

Suitable toggle spanner No. 309840	22
External Ø D	50 mm
Adapter	HSK-A 100 short
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 20,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel Ø 22 mm	309840 22
Milling cutter lock screw for mandrel Ø 22 mm	309860 22