

Garant
Copy mill short, Plain shank, Ø D: 12mm

Order data

Order number	212601 12
GTIN	4045197712639
Item class	210

Description
Version:

Exactly accurate insert bedding due to optimised design of insert and insert seat tolerances. Highest interchange accuracy guaranteed: ± 0.015 mm.

Application:

General use for finishing and semi-finishing operations.

Steel – for general use in machining drop-forgings, and in tool and mould making.

Note:

Calculate the speed based on the effective $\varnothing D_w$. Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size 10IP**.

Technical description

$\varnothing d_1$	10 mm
Cutting edge $\varnothing D_c$	12 mm
Shank $\varnothing D_s$ h6	12 mm
Insert screw	219872 (10IP; 2.2 Nm)
Overhang L_1	32 mm
Overall length L_{tot}	92 mm
Number of cutting edges Z	2
Through-coolant	yes
Shank type	Plain shank
Milling application	Copy milling

Tool exchange	PowerCard
Type of product	Copy mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 10IP	674252 10IP
Torque screwdriver, fixed setting set torque 2,2 N·m	211750 2,2
Clamping screw	219872