



Magnetic measuring stand with fine adjustment at the column, Type: 600



Order data

Order number	441180 600
GTIN	4045197713315
Item class	42D

Description

Version:

Mechanical magnetic measuring stand with central locking mechanism. All three joints are clamped in a single action. Continuously adjustable clamping force with high stability. Ball joints enable quick and easy positioning. Magnetic base with rotary switch and Vee sole. Standard dial indicator mounting for clamping shank \varnothing 6 mm, \varnothing 8 mm and dovetail, fine adjustment at the indicator holder.

Technical description

Magnetic base length	117 mm
Magnetic base height	55 mm
Magnetic base width	50 mm
Magnetic force	1300 N
Length of jointed arm L_2	223 mm
Length of jointed arm L_1	287 mm

maximum loading	14 kg
Throat	580 mm
Connection thread at bottom	M10×1.25
Type of product	measuring stand

Accessories

Stand base Type 2	442120 2
Holder for measuring stand Type QR	442100 QR
Stand base with hydraulic fine adjustment Type 2	440865 2
3-D jointed arm Type 600	442110 600
Holder for measuring stand Type H	442100 H
Holder for measuring stand Type CA	442100 CA
Stand base Type 2	442140 2
Holder for measuring stand Type 2SM	442104 2SM
3-D jointed arm Type 600	442114 600
Holder for measuring stand Type K1	442100 K1
Holder for measuring stand Type 2SM	442100 2SM
Holder for measuring stand Type K2	442100 K2
Stand base Type 2	440868 2
Stand base Type F	442120 F