

Garant
TNMG 160404, Grade: HB7020


Order data

Order number	251432 HB7020
GTIN	4045197711045
Item class	21G

Technical description

Cutting speed v_c main application	150 - 400 m/min
Cutting depth a_p	0.3 - 2 mm
Corner radius	0.4 mm
Chip breaker	SS
Main application	P
Feed f	0.1 - 0.4 mm/rev.
Cutting conditions	slightly interrupted
Grade	HB7020
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TNMG 160404
Number of changes/inserts	6

Type of product

Indexable insert for turning