

Garant
GARANT Master Tap INOX machine tap HSS-E-PM, TiAlN, MF: 14X1,5

Order data

Order number	132875 14X1,5
GTIN	4062406081034
Item class	111

Description
Version:
GARANT Master Tap INOX:

Powerful tap, specially developed for **tapping to high process reliability in stainless and acid-resistant steels** and also **duplex materials**.

- **HSS-E-PM tool material for maximum wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Thread type: MF

Tool material: HSS E PM

Standard: DIN 374

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm

Overall length L: 100 mm

Shank \varnothing D_s: 11 mm

Shank square □: 9 mm

Tapping hole \varnothing : 12.5 mm

Technical description

Thread pitch	1.5 mm
Number of clamping slots	4
Thread type	MF
Overall length L	100 mm
Thread depth	42 mm

Shank square <input type="checkbox"/>	9 mm
Tapping hole \varnothing	12.5 mm
Number of cutting edges Z	4
Tool material	HSS E PM
Tolerance class	ISO 2X 6HX
Standard	DIN 374
Shank $\varnothing D_s$	11 mm
Thread \varnothing	14 mm
Thread size	M14 \times 1.5
Coating	TiAlN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3 \times D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Series	Master Tap
Type of product	Tap

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P

Steel < 1100 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		