

Garant**GARANT Master Tap INOX machine tap HSS-E-PM, TiAlN, G: G3/8****Order data**

Order number	133327 G3/8
GTIN	4062406081133
Item class	11I

Description**Version:****GARANT Master Tap INOX:**

Powerful tap, specially developed for **tapping to high process reliability in stainless and acid-resistant steels** and also **duplex materials**.

- **HSS-E-PM tool material for maximum wear resistance**
- **The latest generation of TiAlN multi-layer coating**
- **Parameterised flute geometry for optimum chip formation and torsional rigidity**

Advantage:

Particularly strong, optimum self-guidance and **no recutting** when reversed.

Application:

For Whitworth parallel pipe threads DIN-ISO 228/1 (threads that do not form a seal within the connection).

Tool material: HSS E PM

Threads per inch: 19

Thread Ø: 16.66 mm

Overall length L: 100 mm

Shank Ø D_s: 12 mm

Shank square □: 9 mm

Tapping hole Ø: 15.25 mm

Technical description

Thread Ø	16.66 mm
Shank Ø D _s	12 mm
Overall length L	100 mm

Number of clamping slots	4
Thread depth	49.98 mm
Tapping hole Ø	15.25 mm
Thread pitch	1.337 mm
Number of cutting edges Z	4
Shank square □	9 mm
Tool material	HSS E PM
Threads per inch	19
Thread size	G3/8
Series	Master Tap
Coating	TiAlN
Thread type	G
Flank angle	55 °
Standard	DIN 5156
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	28 m/min	N
Steel < 750 N/mm ²	suitable only under restricted conditions	23 m/min	P

Steel < 900 N/mm ²	suitable only under restricted conditions	23 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
Oil	suitable		
wet maximum	suitable		