

Garant
VNMG 160404, Grade: HB7020


Order data

Order number	251802 HB7020
GTIN	4045197716965
Item class	21G

Technical description

Feed f	0.1 - 0.5 mm/rev.
Cutting speed v_c main application	120 - 350 m/min
Chip breaker	SM
Corner radius	0.4 mm
Cutting depth a_p	0.5 - 4 mm
Cutting conditions	slightly interrupted
Main application	P
Grade	HB7020
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	VNMG 160404

Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning