

Garant**eco parting-off toolholder with ICS, Shank Ø d1: 50mm****Order data**

Order number	319132 50
GTIN	4045197717207
Item class	31V

Description**Version:**

- **With special adjustable ball type coolant nozzle for optimum cooling of the cutting edge, irrespective of the groove depth.**
- **This reduces the temperature both at the main cutting edge and the auxiliary cutting edge, and permits a significant increase in cutting speed.**
- **Rigid toolholder for parting-off tools.**
- **Blade clamped using clamping plate.**

Application:

Allows parting-off tools of different makes to be used.

Note:

Screw plug for ball spray nozzle included. If conventional grooving tools are used, the lateral coolant transfer is blocked by the grooving tool. Suitable clamping claws No. 279840 2 and suitable screws No. 279815 14. See spare parts list.

Technical description

L ₁	62 mm
Colour code for VDI shanks	VDI 50
suitable for blade height	32 mm

Shank $\varnothing D_1$	50 mm
L_2	100 mm
Height H_1	75.5 mm
Height H_2	47 mm
Type of product	VDI parting-off toolholder